


# Ultra Fast Recovery Rectifiers UFT30, 31 & 32



Dim.	Inches		Millimeter		Notes
	Minimum	Maximum	Minimum	Maximum	
A	—	.875	—	22.23	Dia.
B	.250	.450	6.35	11.43	
C	.312	—	7.92	—	
D	.038	.043	.97	1.09	Dia.
E	1.177	1.197	29.90	30.40	
F	.655	.675	16.64	17.15	
G	.420	.440	10.67	11.18	
H	—	.525	—	13.34	Rad.
J	.151	.161	3.84	4.09	Dia.
K	.205	.225	5.21	5.72	
L	—	.135	—	3.43	
M	—	.188	—	4.78	Rad.

TO-204AA (TO-3)

Microsemi Catalog Number	Working Peak Reverse Voltage	Peak Reverse Voltage
UFT3010*	100V	100V
UFT3015*	150V	150V
UFT3020*	200V	200V
UFT3130*	300V	300V
UFT3140*	400V	400V
UFT3150*	500V	500V
UFT3260*	600V	600V
UFT3270*	700V	700V
UFT3280*	800V	800V

\*Add D, C or A

- Ultra Fast Recovery Rectifier
- 175°C Junction Temperature
- $V_{RRM}$  100 to 800V
- High Reliability
- 30 Amps current rating
- $t_{RR}$  35 to 60 nsec maximum

## Electrical Characteristics Per Leg

	UFT30	UFT31	UFT32	
Average forward current	$I_F(AV)$ 30A	30A	30A	Square wave
Case Temperature (Standard)	$T_C$ 138°C	124°C	122°C	$R_{\theta JC} = 1.4^\circ C/W$
Case Temperature (Reverse)	$T_C$ 115°C	95°C	90°C	$R_{\theta JC} = 2.2^\circ C/W$
Maximum surge current	$I_{FSM}$ 400A	350A	300A	8.3 ms, half sine, $T_J = 175^\circ C$
Max peak forward voltage	$V_{FM}$ .93V	1.10V	1.20V	$I_{FM} = 15A$ : $T_J = 25^\circ C^*$
Max reverse recovery time	$t_{RR}$ 35 ns	50 ns	60 ns	1/2A, 1A, 1/4A, $T_J = 25^\circ C$
Typical reverse recovery time	$t_{RR}$ 26 ns	36 ns	50 ns	1/2A, 1A, 1/4A, $T_J = 25^\circ C$
Max peak reverse current	$I_{RM}$ —	1.0 mA	—	$V_{RRM}$ , $T_J = 125^\circ C$
Max peak reverse current	$I_{RM}$ —	15 $\mu A$	—	$V_{RRM}$ , $T_J = 25^\circ C$
Typical Junction Capacitance	$C_J$ 140 pF	115 pF	100 pF	$V_R = 10V$ , $f = 1MHz$ , $T_J = 25^\circ C$

\*Pulse test: Pulse width 300  $\mu sec$ , Duty cycle 2%

## Thermal and Mechanical Characteristics

Storage temp range	TSTG	-65°C to 200°C
Operating junction temp range	$T_J$	-65°C to 175°C
Max thermal resistance (standard polarity)	$R_{\theta JC}$	1.4°C/W Junction to Case
Max thermal resistance (reverse polarity)	$R_{\theta JC}$	2.2°C/W Junction to Case
Typical thermal resistance (greased)	$R_{\theta CS}$	0.4°C/W Case to sink
Weight		1.0 ounces (28 grams) typical



LAWRENCE

6 Lake Street  
Lawrence, MA 01841  
PH: (978) 620-2600  
FAX: (978) 689-0803  
www.microsemi.com

05-08-07 Rev. 2

# UFT30

Figure 1  
Typical Forward Characteristics – Per Leg




Figure 3  
Typical Junction Capacitance – Per Leg




Figure 4  
Forward Current Derating – Standard Polarity – Per Leg




Figure 2  
Typical Reverse Characteristics – Per Leg





Figure 5  
Forward Current Derating – Reverse Polarity – Per Leg



# UFT30

Figure 6  
Forward Current Derating – Standard Polarity – Per Leg





Figure 7  
Forward Current Derating – Reverse Polarity – Per Leg



# UFT31

Figure 1  
Typical Forward Characteristics – Per Leg




Figure 3  
Typical Junction Capacitance – Per Leg




Figure 4  
Forward Current Derating – Standard Polarity – Per Leg




Figure 2  
Typical Reverse Characteristics – Per Leg





Figure 5  
Forward Current Derating – Reverse Polarity – Per Leg



# UFT31

Figure 6  
Forward Current Derating – Standard Polarity – Per Leg





Figure 7  
Forward Current Derating – Reverse Polarity – Per Leg



# UFT32

Figure 1  
Typical Forward Characteristics – Per Leg




Figure 3  
Typical Junction Capacitance




Figure 4  
Forward Current Derating – Standard Polarity – Per Leg




Figure 2  
Typical Reverse Characteristics – Per Leg





Figure 5  
Forward Current Derating – Reverse Polarity – Per Leg



# UFT32

Figure 6  
Forward Current Derating – Standard Polarity – Per Leg




Figure 7  
Forward Current Derating – Reverse Polarity – Per Leg

